



This document must not be copied without our written permission, and the contents thereof must not be imparted to a third party nor be used for any unauthorized purpose. Contravention will be prosecuted.


1	New drawing template	2019-05-21	MM
Rev.	Description	Date	Sign.



Revision Notice:  
This drawing is not the latest version for the product.  
Minor component modifications are forthcoming,  
but user impact will be negligible.  
Updated drawings expected in November 2023.



General information:  
Power consumption 230 VAC, 50Hz, 6A



4	2	KND508	Filter to spray head, 14 litres/minute
3	2	KND507	Spray head, 14 litres/minute
2	1	KND549	Control card
1	1	KND545	Emergency sign, eye wash
Pos	Quantity	Order number	Description
Owner		Prepared by	Approved by
MM		DK	
Date		2019-05-21	Scale
1:8			
Title		Eye wash station 3893	
Insulated and heated eye wash		Drawing No.	
Installation drawing		R3893	
Rev.		Sheet	
1		1 (1)	