





General information:
Power consumption 230VAC, 50Hz, 6A

This drawing is not the latest version for the product. Minor component modifications are forthcoming, but user impact will be negligible.
Updated drawings expected in November 2023.

2019-06-19 MM Drawing updated Rev. Description Date Sign.

4	2	KND508	Filter to spray head, 14 litres/minute
3	2	KND507	Spray head, 14 litres/minute
2	1	KND549	Control card
1	1	KND545	Emergency sign, eye wash
Pos	Quantity	Order number	Description

DK

Krusman

Phone: +46-(0)21-14 92 00 Website: www.krusman.com

MM

`	Title
J	Eye wash station 3894-00

Insulated and heated eye wash Stainless steel 316 Installation drawing

R3894-00 1 (1)

1:10

2019-06-19